

251-10709

HellermannTyton



Article Number: 251-10709

Description: Grommet, Panel Thickness 0.319"-0.382", PE, Natural, 82ft/pkg

Base Data		
	Local Order Number	FPG
	Type	G51PG
	Color	Natural (NA)
	Features and benefits	• Can be cut to length with scissors, eliminating waste and keeping stock to a minimum. • Available in 9 sizes, for thicknesses from .016" to .512", insuring proper fit.
	Quantity Per	reel
	Product Description	HellermannTyton's Flexiform grommet is a unique, continuous wire protection product which fits easily in all shapes and sizes of holes without the aid of tools or adhesives. Flexiform grommet can be used on any type of material including wood, steel, aluminum, plexiglass, and glass.
	Short Description	Grommet, Panel Thickness 0.319"-0.382", PE, Natural, 82ft/pkg
Product Dimensions		
	Length L (Imperial)	82.0ft
	Reel Length (imperial)	9.7ft
	Variant	Open
	Width W (Imperial)	0.52"
	Width W (Metric)	13.2mm
	Width W2 (Imperial)	0.398"
	Width W2 (Metric)	10.1mm
	Height H (Imperial)	0.268"
	Height H (Metric)	6.8mm
	Height H2 (Imperial)	0.189"
	Height H2 (Metric)	4.8mm
	Panel Thickness Max. (Imperial)	0.382"
	Panel Thickness Max. (Metric)	9.70mm
	Panel Thickness Min. (Imperial)	0.319"

251-10709

HellermannTyton

Product Dimensions	Panel Thickness Min. (Metric)	8.10mm
Material and Specifications		
	Material	Polyethylene (PE)
	Material Shortcut	PE
	Flammability	UL 94 HB
	Halogenfree	Yes
	Operating Temperature	-22°F to +176°F (-30°C to +80°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	82ft
	Package Quantity (Metric)	25m
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	reel
	Weight (Metric)	0.99kg