

300-30957

HellermannTyton

Article Number: 300-30957



Description: Heat Shrink Tubing, .37" Supp, .17" Recov, Polyolefin, Grn/Yel, 16.4ft/pkg

Base Data		
	Local Order Number	300-30957
	Type	HIS-PACK-9.5/4.7
	Color	Green-Yellow (GNYE)
	Features and benefits	<ul style="list-style-type: none"> • Tubing is 2:1, thin wall that provides protection against corrosion and mechanical abrasion. • Available in multiple colors and sizes for easy marking and handling. • Conveniently stored in a handy dispenser box for quick and easy use.
	Quantity Per	box
	Product Description	HIS-PACK Heat Shrink is a general-purpose, thin-wall Polyolefin tubing that provides electrical insulation and protection against corrosion and mechanical abrasion. HIS-PACKs are available in multiple colors and ten sizes ranging from 1/16" (1.2mm) to 1" (25.4mm). Tubing is conveniently stored in a handy dispenser box with hang tag and is RoHS approved.
	Short Description	Heat Shrink Tubing, .37" Supp, .17" Recov, Polyolefin, Grn/Yel, 16.4ft/pkg
Product Dimensions		
	Length L (Imperial)	16.4ft
	Length L (Metric)	5.0m
	Printable (Yes/No)	Yes
	Reel Length (imperial)	16.4ft
	Shrink Ratio	2:1
	Size (imperial)	3/8"
	Trade Size	3/8 "
	Variant	Thin-Wall
	Volume Resistance (Ohm cm)	10 ¹⁴ Ω cm
	Nominal Diameter (Imperial)	3/8"
	Nominal Diameter (Metric)	6.4mm
	Wall Thickness WT (Imperial)	.023"
	Wall Thickness WT (Metric)	0.60mm

300-30957



Product Dimensions	Recovered Diameter d (metric)	4.7mm
	Recovered Diameter d (imperial)	0.17"
	Supplied Diameter D (imperial)	0.37"
	Supplied Diameter D (metric)	9.5mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	20 kV/mm according to IEC 243
	Elongation at break	400% (ASTM D 2671)
	Flammability	UL 224 VW-1 (except clear)
	Halogenfree	No
	Shrink Temperature	+212 °F (+100 °C)
	Operating Temperature	-67°F to +257°F (-55°C to +125°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
	Certification/Specification	SAE - AMS - DTL-23053/5 Class 1 and 3
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	5
	Package Quantity (Metric)	5m
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	0.181kg
	Weight (imperial)	0.4lbs