

401-03044

HellermannTyton

Article Number: 401-03044



Description: Heatshrink Moulded Shapes, 100 series Bottle with Rib - MIL, 103-4-J, PO-X, BK, 1/bag

Base Data		
	Local Order Number	401-03044
	Type	103-4-J
	Color	Black (BK)
	Features and benefits	• Uses a circular grooved adaptor for strain relief. • Combine with complementary adhesives for environmental sealing.
	Quantity Per	bag
	Product Description	Heatshrink 100 series, with rib, is used in conjunction with a circular grooved adaptor providing strain relief and environmental sealing when used in conjunction with one of HellermannTyton's complementary adhesives.
	Short Description	Heatshrink Moulded Shapes, 100 series Bottle with Rib -MIL, 103-4-J, PO-X, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	2mm
	HW ± 20% b (imperial)	.08"
	JW ± 20 % b	2mm
	JW ± 20% b (imperial)	.08"
	H max b (imperial)	1.1"
	H min a (imperial)	1.67"
	J min. a (imperial)	1.67"
	P ±10% b (imperial)	3.86"
	R max.b (imperial)	2.11"
	S nom (imperial)	.94"
	T ± 20% b (imperial)	.07"
	Flexibility	Flexible
	H max b	28.2mm
	H min a	42.7mm
	J max. b	9.9mm

401-03044

HellermannTyton

Product Dimensions	J min. a	42.7mm
	P ±10 % b	99.1mm
	R max.b	54mm
	S nom (metric)	24mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	18 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1