

401-04024

HellermannTyton

Article Number: 401-04024

Description: Heatshrink Moulded Shapes, 100 series Bottle with Rib - MIL, 104-4-G, PO-X, BK, 1/bag



Base Data		
	Local Order Number	401-04024
	Type	104-4-G
	Color	Black (BK)
	Features and benefits	• Uses a circular grooved adaptor for strain relief. • Combine with complementary adhesives for environmental sealing.
	Quantity Per	bag
	Product Description	Heatshrink 100 series, with rib, is used in conjunction with a circular grooved adaptor providing strain relief and environmental sealing when used in conjunction with one of HellermannTyton's complementary adhesives.
	Short Description	Heatshrink Moulded Shapes, 100 series Bottle with Rib -MIL, 104-4-G, PO-X, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	1.3mm
	HW ± 20% b (imperial)	.05"
	JW ± 20 % b	1.3mm
	JW ± 20% b (imperial)	.05"
	H max b (imperial)	.31"
	H min a (imperial)	.64"
	J min. a (imperial)	.64"
	P ±10% b (imperial)	.99"
	R max.b (imperial)	.55"
	S nom (imperial)	.27"
	T ± 20% b (imperial)	.04"
	Flexibility	Semi Rigid
	H max b	7.9mm
	H min a	16.5mm
	J max. b	3.8mm

401-04024

HellermannTyton

Product Dimensions	J min. a	16.5mm
	P ±10 % b	25.4mm
	R max.b	14.2mm
	S nom (metric)	6.9mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	14 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-103°F to +302°F (-75°C to +150°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1