

401-09004

HellermannTyton



Article Number: 401-09004

Description: Heatshrink Moulded Shapes, 100 Series Bottle, 109-1-J, PO-X, BK, 1/bag

Base Data		
	Local Order Number	401-09004
	Type	109-1-J
	Color	Black (BK)
	Features and benefits	• Provides strain relief for connector cable. • Easy re-entry for repair when combined with hot melt adhesive.
	Quantity Per	bag
	Product Description	Heatshrink 100 series, without rib, provides connector cable strain relief. Can be installed on the connector rear thread or plain shaft and allows easy re-entry for repair when combined with a hot melt adhesive.
	Short Description	Heatshrink Moulded Shapes, 100 Series Bottle, 109-1-J, PO-X, BK, 1/bag
Product Dimensions		
	HW $\pm$ 20 % b	2mm
	HW $\pm$ 20% b (imperial)	.08"
	H max b (imperial)	.55"
	H min a (imperial)	.75"
	J min. a (imperial)	.32"
	P $\pm$ 10% b (imperial)	2.08"
	R max.b (imperial)	1.39"
	S nom (imperial)	.3"
	Variant	Thick-Wall
	Flexibility	Flexible
	H max b	14.2mm
	H min a	19.3mm
	J max. b	4.1mm
	J min. a	8.1mm
	P $\pm$ 10 % b	53.3mm

401-09004



Product Dimensions	R max.b	35.6mm
	S nom (metric)	7.6mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	18 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1