

401-10002

HellermannTyton



Article Number: 401-10002

Description: Heatshrink Moulded Shapes, 100 Series Bottle, 110-1-B7, PO-X, BK, 1/bag

Base Data		
	Local Order Number	401-10002
	Type	110-1-B7
	Color	Black (BK)
	Features and benefits	• Provides strain relief for connector cable. • Easy re-entry for repair when combined with hot melt adhesive.
	Quantity Per	bag
	Product Description	Heatshrink 100 series, without rib, provides connector cable strain relief. Can be installed on the connector rear thread or plain shaft and allows easy re-entry for repair when combined with a hot melt adhesive.
	Short Description	Heatshrink Moulded Shapes, 100 Series Bottle, 110-1-B7, PO-X, BK, 1/bag
Product Dimensions		
	HW $\pm$ 20 % b	2.5mm
	HW $\pm$ 20% b (imperial)	.1"
	H max b (imperial)	.69"
	H min a (imperial)	.93"
	J min. a (imperial)	.46"
	P $\pm$ 10% b (imperial)	2.48"
	R max.b (imperial)	1.49"
	S nom (imperial)	.5"
	Variant	Thick-Wall
	Flexibility	Semi Rigid
	H max b	17.8mm
	H min a	23.9mm
	J max. b	5.6mm
	J min. a	11.7mm
	P $\pm$ 10 % b	63.5mm

401-10002

HellermannTyton

Product Dimensions	R max.b	38.1mm
	S nom (metric)	12.7mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	14 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1