

401-13017

HellermannTyton

Article Number: 401-13017



Description: Heatshrink Moulded Shapes, 100 series Bottle with Rib - MIL, 113-4-B7, PO-X, BK, 1/bag

Base Data		
	Local Order Number	401-13017
	Type	113-4-B7
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Uses a circular grooved adaptor for strain relief. • Combine with complementary adhesives for environmental sealing.
	Quantity Per	bag
	Product Description	Heatshrink 100 series, with rib, is used in conjunction with a circular grooved adaptor providing strain relief and environmental sealing when used in conjunction with one of HellermannTyton's complementary adhesives.
	Short Description	Heatshrink Moulded Shapes, 100 series Bottle with Rib -MIL, 113-4-B7, PO-X, BK, 1/bag
Product Dimensions		
	HW \pm 20 % b	1.3mm
	HW \pm 20% b (imperial)	.05"
	H max b (imperial)	.31"
	H min a (imperial)	.42"
	J min. a (imperial)	.18"
	P \pm 10% b (imperial)	.99"
	S nom (imperial)	.18"
	Variant	For plug
	Flexibility	Semi Rigid
	H max b	7.9mm
	H min a	10.7mm
	J max. b	2mm
	J min. a	4.6mm
	P \pm 10 % b	25.4mm
	S nom (metric)	4.6mm

401-13017



Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	14 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1