

401-18022

HellermannTyton

Article Number: 401-18022

Description: Heatshrink Moulded Shapes, 100 series Bottle with Rib - MIL,118-4-J, PO-X, BK, 1/bag



Base Data		
	Local Order Number	401-18022
	Type	118-4-J
	Color	Black (BK)
	Features and benefits	• Uses a circular grooved adaptor for strain relief. • Combine with complementary adhesives for environmental sealing.
	Quantity Per	bag
	Product Description	Heatshrink 100 series, with rib, is used in conjunction with a circular grooved adaptor providing strain relief and environmental sealing when used in conjunction with one of HellermannTyton's complementary adhesives.
	Short Description	Heatshrink Moulded Shapes, 100 series Bottle with Rib -MIL,118-4-J, PO-X, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	3.8mm
	HW ± 20% b (imperial)	.15"
	JW ± 20 % b	3.8mm
	JW ± 20% b (imperial)	.15"
	H max b (imperial)	1.73"
	H min a (imperial)	2.57"
	J min. a (imperial)	2.57"
	P ±10% b (imperial)	5.85"
	R max.b (imperial)	3.12"
	S nom (imperial)	1.88"
	Flexibility	Flexible
	H max b	44.4mm
	H min a	66mm
	J max. b	20.3mm
	J min. a	66mm

401-18022

HellermannTyton

Product Dimensions	P ±10 % b	150mm
	R max.b	80mm
	S nom (metric)	48.3mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	18 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1