

401-30007

# HellermannTyton



Article Number: 401-30007

Description: Heatshrink Moulded Shapes, 130 Series Long Outlet with Rib, 130-1-J, PO-X, BK, 1/bag

|                    |                            |                                                                                                                                                                                 |
|--------------------|----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Base Data          |                            |                                                                                                                                                                                 |
|                    | Local Order Number         | 401-30007                                                                                                                                                                       |
|                    | Type                       | 130-1-J                                                                                                                                                                         |
|                    | Color                      | Black (BK)                                                                                                                                                                      |
|                    | Features and benefits      | <ul style="list-style-type: none"> <li>• Low profile and lightweight.</li> <li>• Typically used on airborne harnesses.</li> <li>• Rib locates on circular backshell.</li> </ul> |
|                    | Quantity Per               | bag                                                                                                                                                                             |
|                    | Product Description        | Heatshrink 130 Series, with rib - VG style, is a low profile and lightweight which is typically used on airborne harnesses. The rib is located on the circular backshell.       |
|                    | Short Description          | Heatshrink Moulded Shapes, 130 Series Long Outlet with Rib, 130-1-J, PO-X, BK, 1/bag                                                                                            |
| Product Dimensions |                            |                                                                                                                                                                                 |
|                    | HW $\pm 20\%$ b            | 1.5mm                                                                                                                                                                           |
|                    | HW $\pm 20\%$ b (imperial) | .06"                                                                                                                                                                            |
|                    | H max b (imperial)         | .59"                                                                                                                                                                            |
|                    | H min a (imperial)         | 1.0"                                                                                                                                                                            |
|                    | J min. a (imperial)        | 1.00"                                                                                                                                                                           |
|                    | P $\pm 10\%$ b (imperial)  | 3.27"                                                                                                                                                                           |
|                    | S nom (imperial)           | 2.36"                                                                                                                                                                           |
|                    | T $\pm 20\%$ b (imperial)  | .04"                                                                                                                                                                            |
|                    | Variant                    | For plug                                                                                                                                                                        |
|                    | H max b                    | 15mm                                                                                                                                                                            |
|                    | H min a                    | 25.2mm                                                                                                                                                                          |
|                    | J max. b                   | 7.5mm                                                                                                                                                                           |
|                    | J min. a                   | 25.5mm                                                                                                                                                                          |
|                    | P $\pm 10\%$ b             | 83mm                                                                                                                                                                            |
|                    | S nom (metric)             | 60mm                                                                                                                                                                            |

401-30007



|                             |                             |                                 |
|-----------------------------|-----------------------------|---------------------------------|
| Material and Specifications |                             |                                 |
|                             | Material                    | Polyolefin, cross-linked (PO-X) |
|                             | Material Shortcut           | PO-X                            |
|                             | Shrink Temperature          | +275 °F (+135 °C)               |
|                             | ROHS Compliant              | Yes                             |
| Logistic and Packaging      |                             |                                 |
|                             | Package Quantity (Imperial) | 1                               |
|                             | Package Quantity (Metric)   | 1                               |