

401-34018

HellermannTyton



Article Number: 401-34018

Description: Heatshrink Moulded Shapes, 130 Series Long Outlet with Rib, 134-4-J, PO-X, BK, 1/bag

| | | |
|--------------------|-----------------------|---|
| Base Data | | |
| | Local Order Number | 401-34018 |
| | Type | 134-4-J |
| | Color | Black (BK) |
| | Features and benefits | <ul style="list-style-type: none"> • Low profile and lightweight. • Typically used on airborne harnesses. • Rib locates on circular backshell. |
| | Quantity Per | bag |
| | Product Description | Heatshrink 130 Series, with rib - VG style, is a low profile and lightweight which is typically used on airborne harnesses. The rib is located on the circular backshell. |
| | Short Description | Heatshrink Moulded Shapes, 130 Series Long Outlet with Rib, 134-4-J, PO-X, BK, 1/bag |
| Product Dimensions | | |
| | HW ± 20 % b | 2mm |
| | HW ± 20% b (imperial) | .08" |
| | JW ± 20 % b | 1.1mm |
| | JW ± 20% b (imperial) | .04" |
| | H max b (imperial) | 1.33" |
| | H min a (imperial) | 1.7" |
| | J min. a (imperial) | 1.7" |
| | P ±10% b (imperial) | 7.92" |
| | S nom (imperial) | 6.36" |
| | T ± 20% b (imperial) | .07" |
| | Variant | For plug |
| | Flexibility | Flexible |
| | H max b | 34mm |
| | H min a | 43.7mm |
| | J max. b | 12.2mm |

401-34018

HellermannTyton

| | | |
|-----------------------------|-----------------------------|-----------------------------------|
| Product Dimensions | J min. a | 43.7mm |
| | P ±10 % b | 203.2mm |
| | S nom (metric) | 163.2mm |
| Material and Specifications | | |
| | Material | Polyolefin, cross-linked (PO-X) |
| | Material Shortcut | PO-X |
| | Flammability | ASTM D635 |
| | Shrink Temperature | +275 °F (+135 °C) |
| | Operating Temperature | -67°F to +275°F (-55°C to +135°C) |
| | ROHS Compliant | Yes |
| Logistic and Packaging | | |
| | Package Quantity (Imperial) | 1 |
| | Package Quantity (Metric) | 1 |