

401-35010

HellermannTyton



Article Number: 401-35010

Description: Heatshrink Moulded Shapes, 130 Series Long Outlet with Rib, 135-4-J, PO-X, BK, 1/bag

Base Data		
	Local Order Number	401-35010
	Type	135-4-J
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Low profile and lightweight. • Typically used on airborne harnesses. • Rib locates on circular backshell.
	Quantity Per	bag
	Product Description	Heatshrink 130 Series, with rib - VG style, is a low profile and lightweight which is typically used on airborne harnesses. The rib is located on the circular backshell.
	Short Description	Heatshrink Moulded Shapes, 130 Series Long Outlet with Rib, 135-4-J, PO-X, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	2.3mm
	HW ± 20% b (imperial)	.09"
	JW ± 20 % b	1.4mm
	JW ± 20% b (imperial)	.05"
	H max b (imperial)	1.61"
	H min a (imperial)	1.95"
	J min. a (imperial)	1.95"
	P ±10% b (imperial)	7.92"
	S nom (imperial)	6.17"
	T ± 20% b (imperial)	.07"
	Variant	For plug
	Flexibility	Flexible
	H max b	41.2mm
	H min a	50mm
	J max. b	14.2mm

401-35010

HellermannTyton

Product Dimensions	J min. a	50mm
	P ±10 % b	203.2mm
	S nom (metric)	158.2mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1