

401-52043

# HellermannTyton

Article Number: 401-52043

Description: Heatshrink Moulded Shapes, 150 series Bottle with Rib - VG, 152-42-G, PO-X, BK, 1/bag



Base Data		
	Local Order Number	401-52043
	Type	152-42-G
	Color	Black (BK)
	Features and benefits	Straight plug-and-socket connector terminal casing as protection against environmental stresses for circular plug connectors, according to VG. The inside lip is used for a reinforced stress relief. Special fitting 199-4-G for audio plugs has external ribs for an improved grip.
	Quantity Per	bag
	Product Description	Heatshrink 150 series, VG style, features an inside lip that is used for a reinforced stress relief. Special fitting 199-4-G for audio plugs has external ribs for an improved grip.
	Short Description	Heatshrink Moulded Shapes, 150 series Bottle with Rib - VG, 152-42-G, PO-X, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	1.6mm
	HW ± 20% b (imperial)	.06"
	JW ± 20 % b	0.5mm
	JW ± 20% b (imperial)	.02"
	H max b (imperial)	.41"
	H min a (imperial)	.94"
	J min. a (imperial)	.94"
	P ±10% b (imperial)	1.48"
	S nom (imperial)	.39"
	Shrink Ratio	4:1
	T ± 20% b (imperial)	.04"
	Variant	For plug
	Flexibility	Semi Rigid
	H max b	10.5mm

401-52043



Product Dimensions	H min. a	24mm
	J max. b	6mm
	J min. a	24mm
	P $\pm$ 10 % b	38mm
	S nom (metric)	10mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	14 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-94°F to +356°F (-70°C to +150°C)
	ROHS Compliant	Yes
	Certification/Specification	LEA
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1
	Weight (Metric)	0.004kg