

401-53041

# HellermannTyton

Article Number: 401-53041

Description: Heatshrink Moulded Shapes, 150 series Bottle with Rib - VG, 153-52-L, FPMX, BK, 1/bag



|                    |                       |                                                                                                                                                                                      |
|--------------------|-----------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Base Data          |                       |                                                                                                                                                                                      |
|                    | Local Order Number    | 401-53041                                                                                                                                                                            |
|                    | Type                  | 153-52-L                                                                                                                                                                             |
|                    | Color                 | Black (BK)                                                                                                                                                                           |
|                    | Features and benefits | <ul style="list-style-type: none"> <li>• Use in conjunction with circular grooved adaptor.</li> <li>• For strain relief and environmental sealing.</li> </ul>                        |
|                    | Quantity Per          | bag                                                                                                                                                                                  |
|                    | Product Description   | Heatshrink 150 series, VG style, features an inside lip that is used for a reinforced stress relief. Special fitting 199-4-G for audio plugs has external ribs for an improved grip. |
|                    | Short Description     | Heatshrink Moulded Shapes, 150 series Bottle with Rib - VG, 153-52-L, FPMX, BK, 1/bag                                                                                                |
| Product Dimensions |                       |                                                                                                                                                                                      |
|                    | HW ± 20 % b           | 1.8mm                                                                                                                                                                                |
|                    | HW ± 20% b (imperial) | .07"                                                                                                                                                                                 |
|                    | H max b (imperial)    | .55"                                                                                                                                                                                 |
|                    | H min a (imperial)    | 1.10"                                                                                                                                                                                |
|                    | J min. a (imperial)   | .28"                                                                                                                                                                                 |
|                    | P ±10% b (imperial)   | 2.16"                                                                                                                                                                                |
|                    | S nom (imperial)      | .63"                                                                                                                                                                                 |
|                    | T ± 20% b (imperial)  | .04"                                                                                                                                                                                 |
|                    | Variant               | For plug                                                                                                                                                                             |
|                    | H max b               | 14mm                                                                                                                                                                                 |
|                    | H min a               | 28mm                                                                                                                                                                                 |
|                    | J max. b              | 3.5mm                                                                                                                                                                                |
|                    | J min. a              | 7mm                                                                                                                                                                                  |
|                    | P ±10 % b             | 55mm                                                                                                                                                                                 |
|                    | S nom (metric)        | 16mm                                                                                                                                                                                 |

401-53041



|                             |                              |                       |
|-----------------------------|------------------------------|-----------------------|
| Material and Specifications |                              |                       |
|                             | Material                     | Fluoroelastomer (FPM) |
|                             | Material Shortcut            | FPMX                  |
|                             | Dielectric Strength (Metric) | 0.8 kV min.           |
|                             | Shrink Temperature           | +347 °F (+175 °C)     |
|                             | ROHS Compliant               | Yes                   |
| Logistic and Packaging      |                              |                       |
|                             | Package Quantity (Imperial)  | 1                     |
|                             | Package Quantity (Metric)    | 1                     |