

401-54005

HellermannTyton

Article Number: 401-54005

Description: Heatshrink Moulded Shapes, 150 series Bottle with Rib - VG, 154-41-J, PO-X, BK, 1/bag



Base Data		
	Local Order Number	401-54005
	Type	154-41-J
	Color	Black (BK)
	Features and benefits	• Use in conjunction with circular grooved adaptor. • For strain relief and environmental sealing.
	Quantity Per	bag
	Product Description	Heatshrink 150 series, VG style, features an inside lip that is used for a reinforced stress relief. Special fitting 199-4-G for audio plugs has external ribs for an improved grip.
	Short Description	Heatshrink Moulded Shapes, 150 series Bottle with Rib - VG, 154-41-J, PO-X, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	1.8mm
	HW ± 20% b (imperial)	.07"
	H max b (imperial)	.55"
	H min a (imperial)	1.17"
	J min. a (imperial)	1.17"
	P ±10% b (imperial)	1.68"
	S nom (imperial)	.51"
	T ± 20% b (imperial)	.04"
	Variant	For plug
	H max b	14mm
	H min a	30mm
	J max. b	6mm
	J min. a	30mm
	P ±10 % b	43mm
	S nom (metric)	13mm

401-54005



Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	12 kV/mm
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1
	Weight (Metric)	0.01