

401-54820

HellermannTyton

Article Number: 401-54820

Description: Heatshrink Moulded Shapes, 150 series Bottle with Rib - VG, 154-42-B7, PO-X, BK, 1/bag



Base Data		
	Local Order Number	401-54820
	Type	154-42-B7
	Color	Black (BK)
	Features and benefits	• Use in conjunction with circular grooved adaptor. • For strain relief and environmental sealing.
	Quantity Per	pieces
	Product Description	Heatshrink 150 series, VG style, features an inside lip that is used for a reinforced stress relief. Special fitting 199-4-G for audio plugs has external ribs for an improved grip.
	Short Description	Heatshrink Moulded Shapes, 150 series Bottle with Rib - VG, 154-42-B7, PO-X, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	1.8mm
	HW ± 20% b (imperial)	.07"
	JW ± 20 % b	1mm
	JW ± 20% b (imperial)	.04"
	H max b (imperial)	.55"
	H min a (imperial)	1.17"
	J min. a (imperial)	1.17"
	P ±10% b (imperial)	2.15"
	S nom (imperial)	.51"
	Shrink Ratio	up to 4.5:1
	T ± 20% b (imperial)	.04"
	Variant	For plug
	H max b	14mm
	H min a	30mm
	J max. b	6mm

401-54820

HellermannTyton

Product Dimensions	J min. a	30mm
	P ±10 % b	55mm
	S nom (metric)	13mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	14 kV/mm
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-103°F to +302°F (-75°C to +150°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
	Certification/Specification	DAN218
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1
	Content Unit (BMEcat)	pieces
	Weight (Metric)	0.01kg