

401-56037

# HellermannTyton

Article Number: 401-56037

Description: Heatshrink Moulded Shapes, 150 series Bottle with Rib - VG, 156-41-J, PO-X, BK, 1/bag



|                    |                       |                                                                                                                                                                                      |
|--------------------|-----------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Base Data          |                       |                                                                                                                                                                                      |
|                    | Local Order Number    | 401-56037                                                                                                                                                                            |
|                    | Type                  | 156-41-J                                                                                                                                                                             |
|                    | Color                 | Black (BK)                                                                                                                                                                           |
|                    | Features and benefits | <ul style="list-style-type: none"> <li>• Use in conjunction with circular grooved adaptor.</li> <li>• For strain relief and environmental sealing.</li> </ul>                        |
|                    | Quantity Per          | bag                                                                                                                                                                                  |
|                    | Product Description   | Heatshrink 150 series, VG style, features an inside lip that is used for a reinforced stress relief. Special fitting 199-4-G for audio plugs has external ribs for an improved grip. |
|                    | Short Description     | Heatshrink Moulded Shapes, 150 series Bottle with Rib - VG, 156-41-J, PO-X, BK, 1/bag                                                                                                |
| Product Dimensions |                       |                                                                                                                                                                                      |
|                    | HW ± 20 % b           | 2.0mm                                                                                                                                                                                |
|                    | HW ± 20% b (imperial) | .08"                                                                                                                                                                                 |
|                    | H max b (imperial)    | .88"                                                                                                                                                                                 |
|                    | H min a (imperial)    | 1.42"                                                                                                                                                                                |
|                    | J min. a (imperial)   | 1.42"                                                                                                                                                                                |
|                    | P ±10% b (imperial)   | 2.36"                                                                                                                                                                                |
|                    | S nom (imperial)      | .79"                                                                                                                                                                                 |
|                    | T ± 20% b (imperial)  | .04"                                                                                                                                                                                 |
|                    | Variant               | For plug                                                                                                                                                                             |
|                    | H max b               | 22.5mm                                                                                                                                                                               |
|                    | H min a               | 36mm                                                                                                                                                                                 |
|                    | J max. b              | 8.5mm                                                                                                                                                                                |
|                    | J min. a              | 36mm                                                                                                                                                                                 |
|                    | P ±10 % b             | 60mm                                                                                                                                                                                 |
|                    | S nom (metric)        | 20mm                                                                                                                                                                                 |

401-56037



|                             |                             |                                 |
|-----------------------------|-----------------------------|---------------------------------|
| Material and Specifications |                             |                                 |
|                             | Material                    | Polyolefin, cross-linked (PO-X) |
|                             | Material Shortcut           | PO-X                            |
|                             | ROHS Compliant              | Yes                             |
| Logistic and Packaging      |                             |                                 |
|                             | Package Quantity (Imperial) | 1                               |
|                             | Package Quantity (Metric)   | 1                               |