

401-78001

HellermannTyton



Article Number: 401-78001

Description: Heatshrink Moulded Shapes, 170 series Bottle with Rib - VG, 178-1-B7, PO-X, BK, 1/bag

| | | |
|--------------------|-----------------------|---|
| Base Data | | |
| | Local Order Number | 401-78001 |
| | Type | 178-1-B7 |
| | Color | Black (BK) |
| | Features and benefits | <ul style="list-style-type: none"> • Cable strain relief for partially loaded connectors • Small cable diameters • Use with our W24 adhesive for excellent chemical resistance |
| | Quantity Per | bag |
| | Product Description | Heatshrink 170 series, with rib, provides cable strain relief in applications of partially loaded connectors, resulting in small cable diameters. When used in conjunction with our W24 adhesive, excellent chemical resistance can also be achieved. |
| | Short Description | Heatshrink Moulded Shapes, 170 series Bottle with Rib - VG, 178-1-B7, PO-X, BK, 1/bag |
| Product Dimensions | | |
| | HW ± 20 % b | 1.8mm |
| | HW ± 20% b (imperial) | .07" |
| | H max b (imperial) | 1.01" |
| | H min a (imperial) | 1.33" |
| | J min. a (imperial) | .37" |
| | P ±10% b (imperial) | 3.31" |
| | S nom (imperial) | 1.99" |
| | T ± 20% b (imperial) | .04" |
| | Variant | For plug |
| | Flexibility | Semi Rigid |
| | H max b | 26mm |
| | H min a | 34mm |
| | J max. b | 3mm |
| | J min. a | 9.5mm |
| | P ±10 % b | 84mm |

401-78001



| | | |
|-----------------------------|------------------------------|-----------------------------------|
| Product Dimensions | S nom (metric) | 51mm |
| Material and Specifications | | |
| | Material | Polyolefin, cross-linked (PO-X) |
| | Material Shortcut | PO-X |
| | Dielectric Strength (Metric) | 14 kV/mm according to ASTM D2671 |
| | Flammability | ASTM D635 |
| | Shrink Temperature | +275 °F (+135 °C) |
| | Operating Temperature | -58°F to +275°F (-50°C to +135°C) |
| | ROHS Compliant | Yes |
| Logistic and Packaging | | |
| | Package Quantity (Imperial) | 1 |
| | Package Quantity (Metric) | 1 |