

401-79013

HellermannTyton



Article Number: 401-79013

Description: Heatshrink Moulded Shapes, 170 series Bottle with Rib - VG, 179-5-L, FPMX, BK, 1/bag

Base Data		
	Local Order Number	401-79013
	Type	179-5-L
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Cable strain relief for partially loaded connectors • Small cable diameters • Use with our W24 adhesive for excellent chemical resistance
	Quantity Per	bag
	Product Description	Heatshrink 170 series, with rib, provides cable strain relief in applications of partially loaded connectors, resulting in small cable diameters. When used in conjunction with our W24 adhesive, excellent chemical resistance can also be achieved.
	Short Description	Heatshrink Moulded Shapes, 170 series Bottle with Rib - VG, 179-5-L, FPMX, BK, 1/bag
Product Dimensions		
	HW $\pm 20\%$ b	1.8mm
	HW $\pm 20\%$ b (imperial)	.07"
	H max b (imperial)	1.33"
	H min a (imperial)	1.7"
	J min. a (imperial)	.28"
	P $\pm 10\%$ b (imperial)	3.9"
	S nom (imperial)	2.26"
	T $\pm 20\%$ b (imperial)	.07"
	Variant	For plug
	Flexibility	Flexible
	H max b	34mm
	H min a	43.5mm
	J max. b	3.5mm
	J min. a	7.2mm
	P $\pm 10\%$ b	100mm

401-79013

HellermannTyton

Product Dimensions	S nom (metric)	58mm
Material and Specifications		
	Material	Fluoroelastomer (FPM)
	Material Shortcut	FPMX
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +392°F (-55°C to +200°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1