

402-03035

HellermannTyton

Article Number: 402-03035

Description: Heatshrink Moulded Shapes, 200 series 2-way Outlet - VG, 203-1-G, PO-X, BK, 1/bag



Base Data		
	Local Order Number	402-03035
	Type	203-1-G
	Color	Black (BK)
	Features and benefits	• Provides mechanical tension relief in cable harnesses.
	Quantity Per	bag
	Product Description	Heatshrink 200 series features branching parts that are employed for mechanical tension relief in cable harnesses.
	Short Description	Heatshrink Moulded Shapes, 200 series 2-way Outlet - VG, 203-1-G, PO-X, BK, 1/bag
Product Dimensions		
	H max b (imperial)	.47"
	H min a (imperial)	1.05"
	J min. a (imperial)	.51"
	P $\pm 10\%$ b (imperial)	3.12"
	S nom (imperial)	1.68"
	Variant	For 2-core cables
	H max b	12mm
	H min a	27mm
	J max. b	6mm
	J min. a	13mm
	P $\pm 10\%$ b	80mm
	S nom (metric)	43mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X

402-03035



Material and Specifications	Dielectric Strength (Metric)	15 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Operating Temperature	-103°F to +302°F (-75°C to +150°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1