

402-06014

HellermannTyton

Article Number: 402-06014

Description: Heatshrink Moulded Shapes, 200 series 2-way Outlet - VG, 206-1-J, PO-X, BK, 1/bag



Base Data		
	Local Order Number	402-06014
	Type	206-1-J
	Color	Black (BK)
	Features and benefits	Provides mechanical tension relief in cable harnesses.
	Quantity Per	bag
	Product Description	Heatshrink 200 series features branching parts that are employed for mechanical tension relief in cable harnesses.
	Short Description	Heatshrink Moulded Shapes, 200 series 2-way Outlet - VG, 206-1-J, PO-X, BK, 1/bag
Product Dimensions		
	H max b (imperial)	.23"
	H min a (imperial)	.51"
	J min. a (imperial)	.27"
	P $\pm 10\%$ b (imperial)	1.6"
	S nom (imperial)	.75"
	Variant	For 2-core cables
	Flexibility	Semi Rigid
	H max b	6mm
	H min a	13mm
	J max. b	3mm
	J min. a	7mm
	P $\pm 10\%$ b	41mm
	S nom (metric)	19mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)

402-06014



Material and Specifications	Material Shortcut	PO-X
	Dielectric Strength (Metric)	15 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-58°F to +176°F (-50°C to +80°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1