

402-17018

HellermannTyton



Article Number: 402-17018

Description: Heatshrink Moulded Shapes, Helashrink 200 Series, 217-2-J, PO-X, BK, 1/bag

Base Data		
	Local Order Number	402-17018
	Type	217-2-J
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Easy, time-saving insulation of cable branch point where it splits into single wires. • Adhesive to relieve mechanical tension in cable harnesses.
	Quantity Per	bag
	Product Description	Helashrink 200 series features branching parts that are used for easy, time-saving insulation of the branch point of a cable where it is split into single wires. Branching parts with adhesive also serve to relieve the mechanical tension in cable harnesses.
	Short Description	Heatshrink Moulded Shapes, Helashrink 200 Series, 217-2-J, PO-X, BK, 1/bag
Product Dimensions		
	HW \pm 20 % b	2.23mm
	HW \pm 20% b (imperial)	.09"
	H max b (imperial)	.59"
	H min a (imperial)	1.21"
	J min. a (imperial)	.51"
	P \pm 10% b (imperial)	3.88"
	S nom (imperial)	.74"
	Shrink Ratio	up to 3:1
	Variant	For 2-core cables
	Flexibility	Semi Rigid
	H max b	15.24mm
	H min a	31mm
	J max. b	4.31mm
	J min. a	13mm
	P \pm 10 % b	99.5mm

402-17018

HellermannTyton

Product Dimensions	S nom (metric)	19mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	15 kV/mm
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +158°F (-55°C to +70°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1