

403-04020

HellermannTyton

Article Number: 403-04020



Description: Heatshrink Moulded Shapes, 300 series 3-way Outlet - VG, 304-50-L, FPMX, BK, 1/bag

Base Data		
	Local Order Number	403-04020
	Type	304-50-L
	Color	Black (BK)
	Features and benefits	• Cable strain relief and mechanical protection at harness transition points.
	Quantity Per	bag
	Product Description	Heatshrink 300 series provides cable strain relief and mechanical protection at harness transition points. All outlets are clearly marked to aid orientation on installation.
	Short Description	Heatshrink Moulded Shapes, 300 series 3-way Outlet - VG, 304-50-L, FPMX, BK, 1/bag
Product Dimensions		
	H max b (imperial)	.53"
	H min a (imperial)	1.05"
	J min. a (imperial)	.49"
	P ±10% b (imperial)	3.63"
	Variant	For 3-core cables
	Flexibility	Flexible
	H max b	13.5mm
	H min a	27mm
	J max. b	7mm
	J min. a	12.5mm
	P ±10 % b	93mm
Material and Specifications		
	Material	Fluoroelastomer (FPM)
	Material Shortcut	FPMX

403-04020



Material and Specifications	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +392°F (-55°C to +200°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1