

403-10015

Article Number: 403-10015



Description: Heatshrink Moulded Shapes, 300 series 3-way Outlet - VG, 310-1-J, PO-X, BK, 1/bag

Base Data		
	Local Order Number	403-10015
	Type	310-1-J
	Color	Black (BK)
	Features and benefits	• Cable strain relief and mechanical protection at harness transition points.
	Quantity Per	bag
	Product Description	Heatshrink 300 series provides cable strain relief and mechanical protection at harness transition points. All outlets are clearly marked to aid orientation on installation.
	Short Description	Heatshrink Moulded Shapes, 300 series 3-way Outlet - VG, 310-1-J, PO-X, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	3mm
	HW ± 20% b (imperial)	.12"
	H max b (imperial)	.74"
	H min a (imperial)	1.5"
	J min. a (imperial)	.74"
	P ±10% b (imperial)	5.27"
	Variant	For 3-core cables
	Flexibility	Flexible
	H max b	19mm
	H min a	38.5mm
	J max. b	10mm
	J min. a	19mm
	P ±10 % b	135mm

403-10015



Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	15 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1