

403-11001

Article Number: 403-11001



Description: Heatshrink Moulded Shapes, 300 series 3-way Outlet - VG, 311-1-B7, PO-X, BK, 1/bag

Base Data		
	Local Order Number	403-11001
	Type	311-1-B7
	Color	Black (BK)
	Features and benefits	• Cable strain relief and mechanical protection at harness transition points.
	Quantity Per	bag
	Product Description	Heatshrink 300 series provides cable strain relief and mechanical protection at harness transition points. All outlets are clearly marked to aid orientation on installation.
	Short Description	Heatshrink Moulded Shapes, 300 series 3-way Outlet - VG, 311-1-B7, PO-X, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	4.5mm
	HW ± 20% b (imperial)	.18"
	H max b (imperial)	.99"
	H min a (imperial)	2.16"
	J min. a (imperial)	1.05"
	P ±10% b (imperial)	7.49"
	Variant	For 3-core cables
	Flexibility	Semi Rigid
	H max b	25.5mm
	H min a	55.5mm
	J max. b	12.5mm
	J min. a	27mm
	P ±10 % b	192mm

403-11001



Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	15 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1