

403-41014

HellermannTyton

Article Number: 403-41014

Description: Heatshrink Moulded Shapes, Helashrink 300 Series, 341-2-J, PO-X, BK, 1/bag



Base Data		
	Local Order Number	403-41014
	Type	341-2-J
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Easy, time-saving insulation of cable branch point where it splits into single wires. • Adhesive to relieve mechanical tension in cable harnesses.
	Quantity Per	bag
	Product Description	Helashrink 300 series features branching parts that are used for easy, time-saving insulation of the branch point of a cable where it is split into single wires. Branching parts with adhesive also serve to relieve the mechanical tension in cable harnesses.
	Short Description	Heatshrink Moulded Shapes, Helashrink 300 Series, 341-2-J, PO-X, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	3.81mm
	HW ± 20% b (imperial)	.15"
	JW ± 20 % b	3.81mm
	JW ± 20% b (imperial)	.15"
	H max b (imperial)	2.3"
	H min a (imperial)	4.88"
	J min. a (imperial)	1.99"
	P ±10% b (imperial)	11.04"
	Shrink Ratio	up to 3:1
	Variant	For 3-core cables
	Flexibility	Flexible
	H max b	58.92mm
	H min a	125mm
	J max. b	25.4mm
	J min. a	51mm

403-41014

HellermannTyton

Product Dimensions	P ±10 % b	283mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	15 kV/mm
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1
	Content Unit (BMEcat)	pieces