

406-08023

HellermannTyton



Article Number: 406-08023

Description: Heatshrink Moulded Shapes, Helashrink 600 Series, 608-2-B7, PO-X, BK, 100/bag

Base Data		
	Local Order Number	406-08023
	Type	608-2-B7
	Color	Black (BK)
	Features and benefits	• Cable breakout boots for insulating and sealing cable crotch or conduit system. • Excellent resistance to abrasion and weathering.
	Quantity Per	box
	Product Description	Cable breakouts are manufactured from a tough cross-linked polyolefin containing a flame retardant. This allows the breakout to be used for both interior and exterior applications. they offer excellent electrical and mechanical protection.
	Short Description	Heatshrink Moulded Shapes, Helashrink 600 Series, 608-2-B7, PO-X, BK, 100/bag
Product Dimensions		
	HW ± 20 % b	3.2mm
	HW ± 20% b (imperial)	.12"
	JW ± 20 % b	3.2mm
	JW ± 20% b (imperial)	.12"
	H max b (imperial)	1.44"
	H min a (imperial)	2.38"
	J min. a (imperial)	.82"
	P ±10% b (imperial)	5.93"
	S nom (imperial)	1.79"
	Shrink Ratio	up to 3:1
	Variant	For plug
	Flexibility	Semi Rigid
	H max b	37mm
	H min a	61mm
	J max. b	9mm

406-08023

HellermannTyton

Product Dimensions	J min. a	21mm
	P ±10 % b	152mm
	S nom (metric)	46mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	14 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100Pieces
	Content Unit (BMEcat)	pieces
	Weight (Metric)	0.074kg