

410-30440

HellermannTyton

Article Number: 410-30440



Description: Heatshrink Moulded Shapes, 100 series Bottle with Rib - MIL, 1030-5-L, FPMX, BK, 1/bag

Base Data		
	Local Order Number	410-30440
	Type	1030-5-L
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Uses a circular grooved adaptor for strain relief. • Combine with complementary adhesives for environmental sealing.
	Quantity Per	pieces
	Product Description	Heatshrink 100 series, with rib, is used in conjunction with a circular grooved adaptor providing strain relief and environmental sealing when used in conjunction with one of HellermannTyton's complementary adhesives.
	Short Description	Heatshrink Moulded Shapes, 100 series Bottle with Rib -MIL, 1030-5-L, FPMX, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	1mm
	HW ± 20% b (imperial)	.04"
	H max b (imperial)	.38"
	H min a (imperial)	.47"
	J min. a (imperial)	.16"
	P ±10% b (imperial)	.74"
	T ± 20% b (imperial)	.02"
	Flexibility	Flexible
	H max b	9.8mm
	H min a	12mm
	J max. b	2mm
	J min. a	4mm
	P ±10 % b	19mm

410-30440



Material and Specifications		
	Material	Fluoropolymer cross-linked (FPMX)
	Material Shortcut	FPMX
	Dielectric Strength (Metric)	9 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +392°F (-55°C to +200°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1
	Customs Number(Schedule B)	-
	Weight (Metric)	0.02kg