

411-07020

HellermannTyton

Article Number: 411-07020



Description: Heatshrink Moulded Shapes, 1100 series 90 degree with Rib -MIL, 1107-4-G, PO-X, BK, 1/bag

Base Data		
	Local Order Number	411-07020
	Type	1107-4-G
	Color	Black (BK)
	Features and benefits	• Used in conjunction with a circular grooved adaptor for strain relief.
	Quantity Per	bag
	Product Description	Heatshrink 1100 series, with rib - MIL style, provides strain relief for harness systems when used in conjunction with a circular grooved adaptor.
	Short Description	Heatshrink Moulded Shapes, 1100 series 90 degree with Rib -MIL, 1107-4-G, PO-X, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	1.5mm
	HW ± 20% b (imperial)	.06"
	H max b (imperial)	.55"
	H min a (imperial)	1.11"
	J min. a (imperial)	1.11"
	P ±10% b (imperial)	1.16"
	S nom (imperial)	.28"
	T ± 20% b (imperial)	.04"
	Variant	For plug
	Flexibility	Semi Rigid
	H max b	14.2mm
	H min a	28.4mm
	J max. b	6.3mm
	J min. a	28.4mm
	P ±10 % b	29.8mm
	S nom (metric)	7.1mm

411-07020



Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	14 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-103°F to +302°F (-75°C to +150°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1