

411-08019

HellermannTyton

Article Number: 411-08019



Description: Heatshrink Moulded Shapes, 1100 series 90 degree with Rib -MIL, 1108-5-L, FPMX, BK, 1/bag

Base Data		
	Local Order Number	411-08019
	Type	1108-5-L
	Color	Black (BK)
	Features and benefits	• Used in conjunction with a circular grooved adaptor for strain relief.
	Quantity Per	bag
	Product Description	Heatshrink 1100 series, with rib - MIL style, provides strain relief for harness systems when used in conjunction with a circular grooved adaptor.
	Short Description	Heatshrink Moulded Shapes, 1100 series 90 degree with Rib -MIL, 1108-5-L, FPMX, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	1mm
	HW ± 20% b (imperial)	.04"
	H max b (imperial)	.31"
	H min a (imperial)	.64"
	J min. a (imperial)	.3"
	P ±10% b (imperial)	.71"
	S nom (imperial)	.2"
	T ± 20% b (imperial)	.04"
	Variant	For plug
	Flexibility	Flexible
	H max b	7.9mm
	H min a	16.5mm
	J max. b	2.5mm
	J min. a	7.6mm
	P ±10 % b	18.3mm
	S nom (metric)	5.1mm

411-08019



Material and Specifications		
	Material	Fluoroelastomer (FPM)
	Material Shortcut	FPMX
	Dielectric Strength (Metric)	9 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +392°F (-55°C to +200°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1