

411-24022

HellermannTyton

Article Number: 411-24022



Description: Heatshrink Moulded Shapes, Series 90 Degree Low Profile with Rib, 1124-1-G, PO-X, BK, 1/bag

Base Data		
	Local Order Number	411-24022
	Type	1124-1-G
	Color	Black (BK)
	Features and benefits	• Lightweight, low profile, compact strain relief and mechanical protection. • Typically used on airborne harnesses.
	Quantity Per	bag
	Product Description	Heatshrink 1100 series, VG style/MIL style, is typically used on airborne harnesses to achieve light weight, low profile, compact strain relief and mechanical protection.
	Short Description	Heatshrink Moulded Shapes, Series 90 Degree Low Profile with Rib, 1124-1-G, PO-X, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	1.8mm
	HW ± 20% b (imperial)	.07"
	H max b (imperial)	.9"
	H min a (imperial)	1.33"
	J min. a (imperial)	1.33"
	P ±10% b (imperial)	3.98"
	S nom (imperial)	2.42"
	T ± 20% b (imperial)	.04"
	Variant	For plug
	Flexibility	Semi Rigid
	H max b	23mm
	H min a	34mm
	J max. b	10mm
	J min. a	34mm
	P ±10 % b	102mm
	S nom (metric)	62mm

411-24022



Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	14 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-103°F to +302°F (-75°C to +150°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1