

411-52001

HellermannTyton

Article Number: 411-52001



Description: Heatshrink Moulded Shapes, 1100 series 90 degree with Rib - VG, 1152-4-B7, PO-X, BK, 1/bag

Base Data		
	Local Order Number	411-52001
	Type	1152-4-B7
	Color	Black (BK)
	Features and benefits	• Used in conjunction with a circular grooved adaptor. • Provides strain relief and an environmental seal.
	Quantity Per	pieces
	Product Description	Heatshrink 1100 series, with rib - VG style, provides strain relief for harness systems when used in conjunction with a circular grooved adaptor. For VG shapes according to T06 with portholes add "P" after the part number.
	Short Description	Heatshrink Moulded Shapes, 1100 series 90 degree with Rib - VG, 1152-4-B7, PO-X, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	1.3mm
	HW ± 20% b (imperial)	.05"
	JW ± 20 % b	0.5mm
	JW ± 20% b (imperial)	.02"
	H max b (imperial)	.41"
	H min a (imperial)	.94"
	J min. a (imperial)	.94"
	S nom (imperial)	.39"
	T ± 20% b (imperial)	.04"
	Variant	For plug
	Flexibility	Semi Rigid
	H max b	10.5mm
	H min a	24mm
	J max. b	6mm
	J min. a	24mm

411-52001

HellermannTyton

Product Dimensions	P ±10 % b	26.0mm
	S nom (metric)	10mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	14 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
	Certification/Specification	DAN341
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1
	Content Unit (BMEcat)	pieces
	Weight (Metric)	0.004kg