

411-59014

HellermannTyton

Article Number: 411-59014



Description: Heatshrink Moulded Shapes, 1100 series 90 degree with Rib - VG,1159-4-G, PO-X, BK, 1/bag

Base Data		
	Local Order Number	411-59014
	Type	1159-4-G
	Color	Black (BK)
	Features and benefits	• Used in conjunction with a circular grooved adaptor. • Provides strain relief and an environmental seal.
	Quantity Per	bag
	Product Description	Heatshrink 1100 series, with rib - VG style, provides strain relief for harness systems when used in conjunction with a circular grooved adaptor. For VG shapes according to T06 with portholes add "P" after the part number.
	Short Description	Heatshrink Moulded Shapes, 1100 series 90 degree with Rib - VG,1159-4-G, PO-X, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	3.8mm
	HW ± 20% b (imperial)	.15"
	JW ± 20 % b	2mm
	JW ± 20% b (imperial)	.08"
	H max b (imperial)	1.76"
	H min a (imperial)	2.57"
	J min. a (imperial)	2.57"
	P ±10% b (imperial)	4.21"
	S nom (imperial)	1.99"
	Shrink Ratio	up to 3:1
	T ± 20% b (imperial)	.08"
	Variant	For plug
	Flexibility	Semi Rigid
	H max b	45mm
	H min a	66mm

411-59014

HellermannTyton

Product Dimensions	J max. b	17mm
	J min. a	66mm
	P ±10 % b	108mm
	S nom (metric)	51mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	14 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-103°F to +302°F (-75°C to +150°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1