

412-07012

HellermannTyton

Article Number: 412-07012



Description: Heatshrink Moulded Shapes, 1200 series T - VG, 1207-1-H, PO-X, BK, 1/bag

Base Data		
	Local Order Number	412-07012
	Type	1207-1-H
	Color	Black (BK)
	Features and benefits	• 4-way outlet shape. • Cable sealing, strain relief and mechanical protection.
	Quantity Per	bag
	Product Description	Heatshrink 1200 series, VG style, provides strain relief, sealing and mechanical protection on cable harnesses.
	Short Description	Heatshrink Moulded Shapes, 1200 series T - VG, 1207-1-H, PO-X, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	2.5mm
	HW ± 20% b (imperial)	.1"
	JW ± 20 % b	2.5mm
	JW ± 20% b (imperial)	.1"
	H max b (imperial)	.48"
	H min a (imperial)	1.05"
	J min. a (imperial)	1.05"
	P ±10% b (imperial)	4.68"
	Variant	For 2-core cables
	Flexibility	Semi Rigid
	H max b	12.4mm
	H min a	26.9mm
	J max. b	12.4mm
	J min. a	26.9mm
	P ±10 % b	120.1mm

412-07012



Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	14 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-103°F to +302°F (-75°C to +150°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1