

413-02008



Article Number: 413-02008

Description: Heatshrink Moulded Shapes, 1300 series 45 angle T - VG,1302-1-H, PO-X, BK, 1/bag

Base Data	Local Order Number	413-02008
	Type	1302-1-H
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Branching part 45 Y-joint • Mechanical tension relief for cable harnesses
	Quantity Per	bag
	Product Description	Heatshrink 1300 series features a branching part 45° (Y-joints) which are employed for mechanical tension relief in cable harnesses.
	Short Description	Heatshrink Moulded Shapes, 1300 series 45 angle T - VG,1302-1-H, PO-X, BK, 1/bag
	Product Dimensions	HW ± 20 % b
HW ± 20% b (imperial)		.1"
JW ± 20 % b		2.5mm
JW ± 20% b (imperial)		.1"
H max b (imperial)		.51"
H min a (imperial)		1.05"
J min. a (imperial)		1.05"
P ±10% b (imperial)		3.59"
S nom (imperial)		1.42"
Variant		For 2-core cables
Flexibility		Semi Rigid
H max b		13mm
H min a		27mm
J max. b		13mm
J min. a		27mm
P ±10 % b		92mm

413-02008



Product Dimensions	S nom (metric)	36mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	14 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-103°F to +302°F (-75°C to +150°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1