

413-03001



Article Number: 413-03001

Description: Heatshrink Moulded Shapes, 1300 series 45 angle T - VG,1303-1-B7, PO-X, BK, 1/bag

Base Data	Local Order Number	413-03001
	Type	1303-1-B7
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Branching part 45 Y-joint. • Mechanical tension relief for cable harnesses.
	Quantity Per	bag
	Product Description	Heatshrink 1300 series features a branching part 45° (Y-joints) which are employed for mechanical tension relief in cable harnesses.
	Short Description	Heatshrink Moulded Shapes, 1300 series 45 angle T - VG,1303-1-B7, PO-X, BK, 1/bag
Product Dimensions	HW ± 20 % b	1.5mm
	HW ± 20% b (imperial)	.06"
	JW ± 20 % b	1.5mm
	JW ± 20% b (imperial)	.06"
	H max b (imperial)	.55"
	H min a (imperial)	1.05"
	J min. a (imperial)	1.05"
	P ±10% b (imperial)	5.66"
	S nom (imperial)	2.13"
	Variant	For 2-core cables
	Flexibility	Semi Rigid
	H max b	14mm
	H min a	27mm
	J max. b	14mm
	J min. a	27mm
P ±10 % b	145mm	

413-03001



Product Dimensions	S nom (metric)	54mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	14 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-94°F to +356°F (-70°C to +150°C)
ROHS Compliant	Yes	
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1