

414-08002

# HellermannTyton



Article Number: 414-08002

Description: Heatshrink Moulded Shapes, 1400 series 90 degree elbow, 1408-2-B7, PO-X, BK, 1/bag

Base Data		
	Local Order Number	414-08002
	Type	1408-2-B7
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Provides strain relief and mechanical protection on cable orientations up to 90°.</li> <li>• Efficient design and numerous material/adhesive combinations provide quick and easy installation across a range of applications.</li> </ul>
	Quantity Per	bag
	Product Description	Heatshrink 1400 series provides strain relief and mechanical protection on cable orientations of up to 90°, efficient design and numerous material/adhesive combinations provide quick and easy installation across a range of applications.
	Short Description	Heatshrink Moulded Shapes, 1400 series 90 degree elbow, 1408-2-B7, PO-X, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	1.8mm
	HW ± 20% b (imperial)	.07"
	JW ± 20 % b	1.8mm
	JW ± 20% b (imperial)	.07"
	H max b (imperial)	.35"
	H min a (imperial)	.74"
	J min. a (imperial)	.74"
	P ±10% b (imperial)	1.74"
	Flexibility	Semi Rigid
	H max b	9mm
	H min a	19mm
	J max. b	9mm
	J min. a	19mm
	P ±10 % b	44.5mm

414-08002



Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	14 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1