

418-07007

Article Number: 418-07007

Description: Heatshrink Moulded Shapes, 1800 series angle with Rib, 1807-5-L, PO-X, BK, 1/bag



Base Data	
Local Order Number	418-07007
Type	1807-5-L
Color	Black (BK)
Features and benefits	<ul style="list-style-type: none"> • Provides strain relief and mechanical protection for harness systems. • Use in conjunction with a circular grooved adaptor.
Quantity Per	bag
Product Description	Helashrink 1800 series, with rib, provides strain relief and mechanical protection for harness systems when used in conjunction with a circular grooved adaptor. Can be supplied in a range of nominal recovered angles and material / adhesive combinations to suit most applications.
Short Description	Heatshrink Moulded Shapes, 1800 series angle with Rib, 1807-5-L, PO-X, BK, 1/bag
Product Dimensions	
HW ± 20 % b	1.8mm
HW ± 20% b (imperial)	.07"
JW ± 20 % b	1.8mm
JW ± 20% b (imperial)	.07"
H max b (imperial)	.71"
H min a (imperial)	.7"
J min. a (imperial)	.58"
P ±10% b (imperial)	1.68"
S nom (imperial)	.12"
T ± 20% b (imperial)	.04"
Flexibility	Flexible
H max b	18.0mm
H min a	18mm
J max. b	7.4mm
J min. a	14.8mm

418-07007



Product Dimensions	P ±10 % b	43.2mm
	S nom (metric)	3.0mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-67°F to +392°F (-55°C to +200°C)
	ROHS Compliant	Yes
Certification/Specification	LEA	
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1