

418-18001

HellermannTyton

Article Number: 418-18001

 Description: Heatshrink Moulded Shapes, 1800 series angle with Rib,
1818-4-G, PO-X, BK, 1/bag


Base Data		
	Local Order Number	418-18001
	Type	1818-4-G
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Provides strain relief and mechanical protection for harness systems. • Use in conjunction with a circular grooved adaptor.
	Quantity Per	bag
	Product Description	Heatshrink 1800 series, with rib, provides strain relief and mechanical protection for harness systems when used in conjunction with a circular grooved adaptor. Can be supplied in a range of nominal recovered angles and material / adhesive combinations to suit most applications.
	Short Description	Heatshrink Moulded Shapes, 1800 series angle with Rib, 1818-4-G, PO-X, BK, 1/bag
Product Dimensions		
	HW $\pm 20\%$ b	2mm
	HW $\pm 20\%$ b (imperial)	.08"
	JW $\pm 20\%$ b	1mm
	JW $\pm 20\%$ b (imperial)	.04"
	H max b (imperial)	1.51"
	H min a (imperial)	2.15"
	J min. a (imperial)	1.48"
	P $\pm 10\%$ b (imperial)	3.28"
	Flexibility	Semi Rigid
	H max b	38.7mm
	H min a	55mm
	J max. b	17.1mm
	J min. a	38mm
	P $\pm 10\%$ b	84mm

418-18001



Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	14 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-103°F to +302°F (-75°C to +150°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1