

418-21001

HellermannTyton

Article Number: 418-21001

Description: Heatshrink Moulded Shapes, 1800 series angle with Rib, 1821-4-G, PO-X, BK, 1/bag



Base Data		
	Local Order Number	418-21001
	Type	1821-4-G
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Provides strain relief and mechanical protection for harness systems. • Use in conjunction with a circular grooved adaptor.
	Quantity Per	bag
	Product Description	Heatshrink 1800 series, with rib, provides strain relief and mechanical protection for harness systems when used in conjunction with a circular grooved adaptor. Can be supplied in a range of nominal recovered angles and material / adhesive combinations to suit most applications.
	Short Description	Heatshrink Moulded Shapes, 1800 series angle with Rib, 1821-4-G, PO-X, BK, 1/bag
Product Dimensions		
	HW ± 20 % b	2.3mm
	HW ± 20% b (imperial)	.09"
	JW ± 20 % b	1.8mm
	JW ± 20% b (imperial)	.07"
	H max b (imperial)	.55"
	H min a (imperial)	.78"
	J min. a (imperial)	.78"
	P ±10% b (imperial)	.94"
	Flexibility	Semi Rigid
	H max b	14.2mm
	H min a	20mm
	J max. b	4.1mm
	J min. a	20mm
	P ±10 % b	24mm

418-21001



Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	14 kV/mm according to ASTM D2671
	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-103°F to +302°F (-75°C to +150°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1