

421-01004

Article Number: 421-01004

Description: Heatshrink Moulded Shapes, 2100 series D boot 90 degree, 2101-1-G, PO-X, BK, 1/bag



Base Data		
	Local Order Number	421-01004
	Type	2101-1-G
	Color	Black (BK)
	Features and benefits	Provides strain relief and mechanical protection for Min-D series connectors
	Quantity Per	bag
	Product Description	Heatshrink 2100 series, with 90° entry, features a unique design that allows perfect 90° orientation on installation. It can be supplied with or without lips in a range of material and adhesive combinations to suit most applications.
	Short Description	Heatshrink Moulded Shapes, 2100 series D boot 90 degree, 2101-1-G, PO-X, BK, 1/bag
Product Dimensions		
	H max b (imperial)	.79"
	H min a (imperial)	.79"
	J min. a (imperial)	.42"
	P ±10% b (imperial)	1.01"
	Flexibility	Semi Rigid
	H max b	20.3mm
	H min a	20.3mm
	J max. b	10.7mm
	J min. a	10.7mm
	P ±10 % b	25.9mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	14 kV/mm according to ASTM D2671

421-01004



Material and Specifications	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-103°F to +302°F (-75°C to +150°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1