

421-02004

Article Number: 421-02004



Description: Heatshrink Moulded Shapes, 2100 series D boot 90 degree, 2102-1-G, PO-X, BK, 1/bag

Base Data		
	Local Order Number	421-02004
	Type	2102-1-G
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> Provides strain relief and mechanical protection for Min-D series connectors
	Quantity Per	bag
	Product Description	Heatshrink 2100 series, with 90° entry, features a unique design that allows perfect 90° orientation on installation. It can be supplied with or without lips in a range of material and adhesive combinations to suit most applications.
	Short Description	Heatshrink Moulded Shapes, 2100 series D boot 90 degree, 2102-1-G, PO-X, BK, 1/bag
Product Dimensions		
	H max b (imperial)	1.1"
	H min a (imperial)	1.1"
	J min. a (imperial)	.41"
	P ±10% b (imperial)	1.2"
	Flexibility	Semi Rigid
	H max b	28.2mm
	H min a	28.1mm
	J max. b	10.7mm
	J min. a	10.6mm
	P ±10 % b	30.7mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	14 kV/mm according to ASTM D2671

421-02004



Material and Specifications	Flammability	ASTM D635
	Shrink Temperature	+275 °F (+135 °C)
	Operating Temperature	-103°F to +302°F (-75°C to +150°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1