

422-00505

HellermannTyton



Article Number: 422-00505

Description: Heatshrink Moulded Shapes, Heatshrink shapes - low profile, 313C774-6, PO-X, BK, 5/bag

Base Data		
	Local Order Number	422-00505
	Type	313C774-6
	Color	Black (BK)
	Features and benefits	• Used in conjunction with a circular grooved adaptor for strain relief.
	Quantity Per	bag
	Product Description	Heatshrink 313C series is used with a circular grooved adaptor to provide strain relief and if adhesive is used, excellent environmental sealing can be achieved. The convoluted design provides the flexibility to accommodate different cable outlet angles.
	Short Description	Heatshrink Moulded Shapes, Heatshrink shapes - low profile, 313C774-6, PO-X, BK, 5/bag
Product Dimensions		
	H max b (imperial)	1.58"
	H min a (imperial)	3.01"
	J min. a (imperial)	2.13"
	P $\pm 10\%$ b (imperial)	9.21"
	R max.b (imperial)	2.43"
	Shrink Ratio	3:1
	Variant	For plug
	Flexibility	Flexible
	H max b	4.6mm
	H min a	77.2mm
	J max. b	22.8mm
	J min. a	54.6mm
	P $\pm 10\%$ b	236.2mm
	R max.b	62.2mm

422-00505



Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	20 kV/mm
	Flammability	ASTM D635
	Shrink Temperature	+212 °F (+100 °C)
	Operating Temperature	-67°F to +248°F (-55°C to +120°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	5
	Package Quantity (Metric)	5Pieces