

422-20021

HellermannTyton



Article Number: 422-20021

Description: Heatshrink Moulded Shapes, Straight boot, 313F322-8, PEEX, BK, 5/bag

Base Data		
	Local Order Number	422-20021
	Type	313F322-8
	Color	Black (BK)
	Features and benefits	• Connector strain relief for small cable diameters requiring high shrink ratio.
	Quantity Per	bag
	Product Description	This boot provides strain relief in applications with partially loaded connectors, resulting in small cable diameters requiring a high shrink ratio.
	Short Description	Heatshrink Moulded Shapes, Straight boot, 313F322-8, PEEX, BK, 5/bag
Product Dimensions		
	H max b (imperial)	.39"
	H min a (imperial)	.93"
	J min. a (imperial)	.69"
	P ±10% b (imperial)	4.13"
	Shrink Ratio	3:1
	Variant	For plug
	Flexibility	Flexible
	H max b	9.9mm
	H min a	23.8mm
	J max. b	8.1mm
	J min. a	17.7mm
	P ±10 % b	105.9mm
Material and Specifications		
	Material	Polyester elastomer cross-linked (PEEX)
	Material Shortcut	PEEX

422-20021



Material and Specifications	Flammability	ASTM D635
	Shrink Temperature	+212 °F (+100 °C)
	Operating Temperature	-67°F to +302°F (-55°C to +150°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	5
	Package Quantity (Metric)	5Pieces