

422-30512

# HellermannTyton



Article Number: 422-30512

Description: Heatshrink Moulded Shapes, Long tail right angle boot, 333F332-8, PEEX, BK, 5/bag

Base Data	
Local Order Number	422-30512
Type	333F332-8
Color	Black (BK)
Features and benefits	• Connector strain relief for small cable diameters requiring high shrink ratio.
Quantity Per	bag
Product Description	Helashrink 313C series is used with a circular grooved adapter to provide strain relief and if adhesive is used, excellent environmental sealing can be achieved. The convoluted design provides the flexibility to accommodate different cable outlet angles.
Short Description	Heatshrink Moulded Shapes, Long tail right angle boot, 333F332-8, PEEX, BK, 5/bag
Product Dimensions	
H max b (imperial)	.51"
H min a (imperial)	1.06"
J min. a (imperial)	.81"
P ±10% b (imperial)	4.52"
Shrink Ratio	3:1
Variant	For plug
Flexibility	Flexible
H max b	13.2mm
H min a	27.1mm
J max. b	7.6mm
J min. a	2.8mm
P ±10 % b	115.8mm
Material and Specifications	
Material	Polyester elastomer cross-linked (PEEX)

422-30512



Material and Specifications	Material Shortcut	PEEX
	Flammability	ASTM D635
	Shrink Temperature	+212 °F (+100 °C)
	Operating Temperature	-67°F to +248°F (-55°C to +120°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	5
	Package Quantity (Metric)	5Pieces