

422-40100

HellermannTyton



Article Number: 422-40100

Description: Heatshrink Moulded Shapes, Transition T boot, 412H623-9, PO-X, BK, 5/bag

Base Data		
	Local Order Number	422-40100
	Type	412H623-9
	Color	Black (BK)
	Features and benefits	• Connector cable strain relief. • Used with circular adapter.
	Quantity Per	bag
	Product Description	Heatshrink 412H series provides connector cable strain relief and is used in conjunction with a circular adapter.
	Short Description	Heatshrink Moulded Shapes, Transition T boot, 412H623-9, PO-X, BK, 5/bag
Product Dimensions		
	H max b (imperial)	.44"
	H min a (imperial)	1.33"
	J min. a (imperial)	.89"
	P $\pm 10\%$ b (imperial)	4.69"
	Shrink Ratio	3:1
	Variant	For 2-core cables
	Flexibility	Semi Rigid
	H max b	11.4mm
	H min a	34.2mm
	J max. b	6.6mm
	J min. a	22.8mm
	P $\pm 10\%$ b	120.3mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X

422-40100



Material and Specifications	Dielectric Strength (Metric)	20 kV/mm according to IEC 243
	Flammability	ASTM D635
	Shrink Temperature	+212 °F (+100 °C)
	Operating Temperature	-67°F to +248°F (-55°C to +120°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	5
	Package Quantity (Metric)	5Pieces
	Content Unit (BMEcat)	pieces
	Weight (Metric)	0.008kg