

422-50101

HellermannTyton



Article Number: 422-50101

Description: Heatshrink Moulded Shapes, Transition Y boot, 492H413-9, PO-X, BK, 5/bag

Base Data		
	Local Order Number	422-50101
	Type	492H413-9
	Color	Black (BK)
	Features and benefits	• For cable harness breakouts or transitions. • Strain relief, sealing and mechanical protection.
	Quantity Per	bag
	Product Description	Heatshrink 492H series provides strain relief, sealing and mechanical protection on cable harness breakouts or transitions.
	Short Description	Heatshrink Moulded Shapes, Transition Y boot, 492H413-9, PO-X, BK, 5/bag
Product Dimensions		
	H max b (imperial)	.44"
	H min a (imperial)	1.33"
	J min. a (imperial)	.89"
	P $\pm 10\%$ b (imperial)	4.73"
	Shrink Ratio	3:1
	Variant	For 2-core cables
	Flexibility	Flexible
	H max b	11.4mm
	H min a	34.2mm
	J max. b	11.4mm
	J min. a	22.8mm
	P $\pm 10\%$ b	121.4mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X

422-50101



Material and Specifications	Dielectric Strength (Metric)	20 kV/mm according to IEC 243
	Flammability	ASTM D635
	Shrink Temperature	+212 °F (+100 °C)
	Operating Temperature	-67°F to +248°F (-55°C to +120°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	5
	Package Quantity (Metric)	5Pieces
	Content Unit (BMEcat)	pieces
	Weight (Metric)	0.009kg