

422-60202

HellermannTyton

Article Number: 422-60202

Description: Heatshrink Moulded Shapes, Transition 3-way boot, 573H534-9, PO-X, BK, 5/bag



Base Data		
	Local Order Number	422-60202
	Type	573H534-9
	Color	Black (BK)
	Features and benefits	• For cable harness breakouts or transitions. • Strain relief, sealing and mechanical protection.
	Quantity Per	bag
	Product Description	Heatshrink 573H series provides strain relief, sealing and mechanical protection on cable harness breakouts or transitions.
	Short Description	Heatshrink Moulded Shapes, Transition 3-way boot, 573H534-9, PO-X, BK, 5/bag
Product Dimensions		
	H max b (imperial)	.78"
	H min a (imperial)	2.34"
	J min. a (imperial)	1.40"
	P $\pm 10\%$ b (imperial)	8.08"
	Shrink Ratio	3:1
	Variant	For 3-core cables
	Flexibility	Flexible
	H max b	20.0mm
	H min a	60.1mm
	J max. b	20.0mm
	J min. a	36.0mm
	P $\pm 10\%$ b	207.2mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X

422-60202



Material and Specifications	Dielectric Strength (Metric)	20 kV/mm according to IEC 243
	Flammability	ASTM D635
	Shrink Temperature	+212 °F (+100 °C)
	Operating Temperature	-67°F to +248°F (-55°C to +120°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	5
	Package Quantity (Metric)	5Pieces
	Content Unit (BMEcat)	pieces
	Weight (Metric)	0.021kg