

553-50211



Article Number: 553-50211

Description: Heat Shrink Labels, .125" (3.17mm), Single Sided, 3-Slit LB, PO-X, White, 4000/box



Base Data		
	Local Order Number	553-50211
	Type	HST3-1WH-3S
	Color	White (WH)
	Features and benefits	• Slide Slit and optional center slits for easy wire insertion. • Smooth surface for clean and legible printing. • Supplied on a ladder style carrier so that markers can be kitted after printing. • A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.
	Quantity Per	box
	Product Description	HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.
	Local Order Number 2	THS-610W3P10C
	Short Description	Heat Shrink Labels, .125" (3.17mm), Single Sided, 3-Slit LB, PO-X, White, 4000/box
Product Dimensions		
	Length L (Imperial)	0.475"
	Length L (Metric)	12.07mm
	Printable (Yes/No)	Yes
	Variant	Thin-Wall
	Height H (Imperial)	.60"
	Height H (Metric)	15.16mm
	Diameter Max. (Imperial)	0.375"
	Diameter Max. (Metric)	9.53mm
	Outside Diameter Max. (Imperial)	0.125"
	Outside Diameter Max. (Metric)	3.2mm
	Wall Thickness WT (Imperial)	0.0209"
	Wall Thickness WT (Metric)	0.53mm

553-50211



Product Dimensions	Flexibility	Flexible
	Print Method	Thermal transfer
	Recovered Diameter d (metric)	1.1mm
	Recovered Diameter d (imperial)	0.043"
	Supplied Diameter D (imperial)	0.118"
	Supplied Diameter D (metric)	3.0mm
	Thickness T (Metric)	3.0µm
	Width of Liner WL (imperial)	3.0"
	Width of Liner WL (metric)	76.2mm
	Width of printable area (metric)	12.07mm
	Width of Printable Area (imperial)	0.475"
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	US MILSPEC	SAE-AS81531
	Dielectric Strength (Metric)	19.7 kV min.
	Flammability	UL 224 VW-1
	Shrink Temperature	+194 °F (+90 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	ROHS Compliant	Yes
	Certification/Specification	CEN
Logistic and Packaging		
	Package Quantity (Imperial)	4000
	Package Quantity (Metric)	4000
	Markers per row	4
	Weight (Metric)	1.176kg
	Weight (imperial)	2.56