

553-50231



Article Number: 553-50231

Description: Heat Shrink Labels, .5" (12.7mm), Single Sided, Unslit, PO-X, White, 1000/box



Base Data		
	Local Order Number	553-50231
	Type	HST12-4WH
	Color	White (WH)
	Features and benefits	• Slide Slit and optional center slits for easy wire insertion. • Smooth surface for clean and legible printing. • Supplied on a ladder style carrier so that markers can be kitted after printing. • A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.
	Quantity Per	box
	Product Description	HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.
	Short Description	Heat Shrink Labels, .5" (12.7mm), Single Sided, Unslit, PO-X, White, 1000/box
Product Dimensions		
	Length L (Imperial)	0.77"
	Length L (Metric)	19.55mm
	Printable (Yes/No)	Yes
	Variant	Thin-Wall
	Width W (Imperial)	1.90"
	Width W (Metric)	48mm
	Height H (Imperial)	.77"
	Height H (Metric)	19.55mm
	Diameter Max. (Imperial)	0.5"
	Outside Diameter Max. (Imperial)	0.5"
	Outside Diameter Max. (Metric)	12.7mm
	Wall Thickness WT (Imperial)	0.033"
	Wall Thickness WT (Metric)	0.84mm

553-50231



Product Dimensions	Flexibility	Flexible
	Print Method	Thermal transfer
	Recovered Diameter d (metric)	4.2mm
	Recovered Diameter d (imperial)	0.166"
	Supplied Diameter D (metric)	11.9mm
	Supplied Diameter D (imperial)	0.47"
	Thickness T (Metric)	3.0µm
	Width of Liner WL (imperial)	3.0"
	Width of Liner WL (metric)	76.2mm
	Width of printable area (metric)	48.26mm
	Width of Printable Area (imperial)	1.9"
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	US MILSPEC	SAE-AS81531
	Dielectric Strength (Metric)	19.7 kV/mm
	Flammability	UL 224 VW-1
	Shrink Temperature	+194 °F (+90 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	ROHS Compliant	Yes
	Certification/Specification	UL224 125 °C 600V VW-1
Logistic and Packaging		
	Package Quantity (Imperial)	1000
	Package Quantity (Metric)	1000
	Markers per row	1
	Weight (imperial)	4.56
	Weight (Metric)	2.08kg