

556-00143

HellermannTyton



Article Number: 556-00143

Description: Thermal Transfer Ribbon, 4.33" x 295', .50" Core, DTH Resin, Black, 1/pkg

Base Data		
	Local Order Number	TTDTHOUTSM
	Type	TTDTHOUTSM
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Ribbons are resin based for the best print durability. • Ribbons are available to fit all HellermannTyton printers for easy resupply. • Ribbons are available in colors for maximizing design printing capabilities. • Ribbons meet UL recognition and Military standard where applicable to meet specific industry label requirements.
	Quantity Per	EA
	Product Description	Thermal Transfer Ribbons are designed for use in HellermannTyton thermal transfer printers. Available on 1/2" and 1" cores, the ribbons are coated side out and available in different lengths. All ribbons are available in a variety of colors and are matched to the HellermannTyton label stock to give the best chemical and abrasion resistance.
	Short Description	Thermal Transfer Ribbon, 4.33" x 295', .50" Core, DTH Resin, Black, 1/pkg
Product Dimensions		
	Length L (Imperial)	242.0ft
	Length L (Metric)	74.0m
	Reel Length (imperial)	242.0ft
	Variant	Colored ribbon
	Width W (Imperial)	4.33"
	Width W (Metric)	110.0mm
	Print Method	Thermal transfer
Material and Specifications		
	Material	Polyester (PET)
	Material Shortcut	PET
	Halogenfree	Yes
	Operating Temperature	+40°F to +300°F (+4°C to +82°C)

556-00143

HellermannTyton

Material and Specifications	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1
	Customs Number(Schedule B)	9612101000
	Weight (Metric)	0.1kg